



Motorola XT1033 Distancia focal: 3.5mm 1/571s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3.5mm 1/681s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3.5mm 1/478s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3.5mm 1/665s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3.5mm 1/110s f2.4 ISO: 1600



Motorola XT1033 Distancia focal: 3.5mm 1/12128s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3.5mm 1/1370s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3.5mm 1/980s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3.5mm 1/3025s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3.5mm 1/1087s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3.5mm 1/2273s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3.5mm 1/1370s f2.4 ISO: 125





Motorola XT1033 Distancia focal: 3,5mm 1/1370s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3,5mm 1/901s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3,5mm 1/1370s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3,5mm 1/681s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3,5mm 1/1124s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3,5mm 1/552s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3,5mm 1/617s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3,5mm 1/541s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3,5mm 1/2273s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3,5mm 1/77s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3,5mm 1/202s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3,5mm 1/30s f2.4 ISO: 160





Motorola XT11033 Distância focal: 3,5mm 1/10s f2.4 ISO: 1600



Motorola XT11033 Distância focal: 3,5mm 1/10s f2.4 ISO: 1600

