



Motorola XT1033 Distancia focal: 3,5mm 1/1124s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3,5mm 1/608s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3,5mm 1/130s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3,5mm 1/685s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3,5mm 1/60s f2.4 ISO: 200



Motorola XT1033 Distancia focal: 3,5mm 1/60s f2.4 ISO: 160



Motorola XT1033 Distancia focal: 3,5mm 1/150s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3,5mm 1/1124s f2.4 ISO: 125




Motorola XT1033 Distancia focal: 3,5mm 1/437s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3,5mm 1/541s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3,5mm 1/2438s f2.4 ISO: 125



Motorola XT1033 Distancia focal: 3,5mm 1/524s f2.4 ISO: 125



Motorola XT1033 Distância focal: 3.5mm 1/891s f/2.4 ISO: 125



Motorola XT1033 Distância focal: 3.5mm 1/926s f/2.4 ISO: 125



Motorola XT1033 Distância focal: 3.5mm 1/476s f/2.4 ISO: 125



Motorola XT1033 Distância focal: 3.5mm 1/1087s f/2.4 ISO: 125



Motorola XT1033 Distância focal: 3.5mm 1/202s f/2.4 ISO: 125



Motorola XT1033 Distância focal: 3.5mm 1/166s f/2.4 ISO: 125